

## Indirect Tensile Fatigue Measurement Test System



### CRT-FAT-SET

Indirect tensile fatigue measurement system to perform EN 12697-24 (Annex E)

- Requires CRT-IT-SET Sub-frame
- 2\* CRT-SPTLVDT displacement transducer  $\pm 1.0\text{mm}$  range
- On specimen fatigue clamping frame for 100mm  $\varnothing$  specimens
- Setup jig
- 1\* 7mm spanner
- Test software to meet latest standard specifications

*Datasheet Version: 19.01/01*